

Foxx Life Sciences EZFlow, Assembly with Glass Membrane



Description • Foxx Life Science EZflow Glass Filtration is great for filtration of particulate contamination

- The assemblies feature an all glass assembly that is made from high quality ingredients
- It includes a flask, funnel cup, membrane holder, and an aluminum clamp
- The glass filtration has high resistant to acid, chlorine bromine, iodine and organic substances
- Due to its resistance to heat, corrosion, and thermal shock, our glass filtration can be used in many applications

Specifications

- Material: Glass
- Membrane Holder Diameter: 25 mm
- Clamp material: Aluminum

Image(s) are representative of the product group and not necessarily the individual product.

Order	29-Apr-2024 12:52: PM PDT	PRICES ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTICE.					
Catalog	Item	Availability	Manufacturer	Mfg. Part #	NDC#	Your Price	Unit
621-13542-EA	Foxx Life Sciences EZFlow, Assembly, 125 mL Flask, 15 mL Funnel w/25 mm Glass Membrane - 1 ea Flask Volume (mL): 125 Funnel Cup Volume (mL): 15 Dimensions L x W x H (in.): 5.5 x 3 x 9.75 	Sign In		34R-1001-FLS			EA
621-13548-EA	Foxx Life Sciences EZFlow, Assembly, 250 mL Flask, 30 mL Funnel w/25 mm Glass Membrane - 1 ea Flask Volume (mL): 250 Funnel Cup Volume (mL): 25 Dimensions L x W x H (in.): 6 x 3.5 x 12 			34R-2001-FLS			EA
621-13554-EA	Foxx Life Sciences EZFlow, Assembly, 500 mL Flask, 50 mL Funnel w/25 mm Glass Membrane - 1 ea Flask Volume (mL): 500 Funnel Cup Volume (mL): 50 Dimensions L x W x H (in.): 7 x 4.5 x 14 			34R-3001-FLS			EA