






Veltek ASEPTI-CLEANSE Dispenser

Description • Several options exist to simplify the dispensing of VAI products

- The DEC-50 minimizes cross-contamination by enabling the user to simply place the back of their gloved hand on the DEC-50 Actuation Arm to dispense VAI products rather than handle the container
- The pump and trigger spray mechanisms simplify dispensing VAI products while delivering dosed quantities to prevent overuse
- ASEPTI-CLEANSE is a hands-free dispensing system for select VAI products
- VAI developed the ASEPTI-CLEANSE to meet the requirements of cGMP clean room operations
- The dispensing system is the most advanced infrared sensor dispensing system available in the pharmaceutical and biotechnology industries
- ASEPTI-CLEANSE can be mounted directly to glass or walls, which makes it an excellent choice for gowning rooms and aseptic manufacturing areas
- It can be set to dispense approximately 1, 2, or 3 mL of solution
- Simply place your hand underneath the ASEPTI-CLEANSE to deliver a pre-measured dose of solution, to the hand, with no contact between the user and the ASEPTI-CLEANSE
- Our ASEPTI-CLEANSE system works exclusively with our DECON-HAND and DECON-AHOL WFI Formula



- The ASEPTI-CLEANSE Bottles use a new and improved ASEPTI-CLEANSE operating system
- · Photo-eye operated
- Equipped with dual power supply
- 4 D Cell batteries (Can last over 1 year)
- Connector for Aux. DC power in
- Mountable directly on glass or walls
- Water resistant
- Americans with Disabilities Act (ADA) compliant
- UL Medical Device listed
- Able to be maintai

Order	29-Apr-2024 01:43: AM PDT	PRICES ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTICE.					
Catalog	Item	Availability	Manufacturer	Mfg. Part #	NDC#	Your Price	Unit
120-97705- EA	Veltek Associates, Inc. Veltek Dispenser, ASEPTI-CLEANSE - 1 ea	Sign In	Veltek Associates, Inc.				EA

